

# METALWRAP-H w/MR-100

INTERIOR SIDE  
MEMBRANE FLASHING;  
CONTINUOUS TO BASE.

NOTCH PANEL LINER AT  
CORNERS AS SHOWN  
(PROVIDES A THERMAL  
BREAK)

SEALANT BETWEEN  
PANEL LINER AND  
INTERIOR MEMBRANE

CSC-3 FLUSH  
PANEL CLIP

1½" SUBFRAMING  
AND AIR CAVITY

CONCEPT SERIES  
CS-260 PANEL  
(MITERED CORNER)

METALWRAP PANEL;  
FIELD CUT AS REQ'D

CONTINUOUS MR-100  
ATTACHMENT SYSTEM AT EACH  
PANEL SIDE JOINT (36" O.C.)  
VERTICALLY AND FASTENED  
INTO EACH FRAMING MEMBER  
(16" TO 24" O.C.)  
HORIZONTALLY

STEEL STUD  
18 GA. MIN.

INTERIOR  
GYPSUM  
BOARD

MINIMUM SEALANT  
CONTACT SHOWN

3/8" MIN.

FLASHING TAPE  
@ VERT. JOINTS

SEALANT PLUG DETAIL  
APPLY SEALANT AS  
PANELS ARE ERECTED.

## NOTE:

THESE DETAILS ARE FOR INSTALLATION  
AND SEALING OF METALWRAP PANELS  
ONLY. FOR INSTALLATION AND SEALING  
REQUIRED FOR FACE PANELS SEE CENTRIA  
STANDARD DETAILS FOR THE SPECIFIC  
FACE PANEL.

# METALwrap

Outside 90° Concept Series Mitered Corner  
MR100-09A

JANUARY 2018