

# METALWRAP-H w/MR-100

NOTCH PANEL FACE AT CORNERS AS SHOWN (PROVIDES A THERMAL BREAK)

APPLY A CURING BUTYL SEALANT PLUG NEAR EACH PANEL END DURING PANEL ERECTION. (SEE DETAIL BELOW)

SEALANT BETWEEN PANEL LINER AND CORNER FLASH

CONTINUOUS INTERIOR SIDE CORNER FLASHING

6" WIDE EXTERIOR SIDE MEMBRANE OR METAL FLASHING; CONTINUOUS ONTO BASE FLASHING BELOW.

INTERIOR GYPSUM BOARD

MINIMUM SEALANT CONTACT SHOWN

3/8" MIN.

FLASHING TAPE @ VERT. JOINTS.

SEALANT PLUG DETAIL  
APPLY SEALANT AS  
PANELS ARE ERECTED.

STEEL STUD  
18 GA. MIN.

CSC-3 FLUSH  
PANEL CLIP

3/4" SUBFRAMING  
AND AIR CAVITY

METAL CLOSURES

2 1/2" MIN.

CONTINUOUS MR-100  
ATTACHMENT SYSTEM AT EACH  
PANEL SIDE JOINT (36" O.C.)  
VERTICALLY AND FASTENED  
INTO EACH FRAMING MEMBER  
(16" TO 24" O.C.)  
HORIZONTALLY

CONCEPT SERIES  
CS-260 PANEL

METALWRAP PANEL;  
FIELD CUT AS REQ'D

## NOTE:

THESE DETAILS ARE FOR INSTALLATION AND SEALING OF METALWRAP PANELS ONLY. FOR INSTALLATION AND SEALING REQUIRED FOR FACE PANELS SEE CENTRIA STANDARD DETAILS FOR THE SPECIFIC FACE PANEL.

# METALwrap

Inside 90° Corner  
MR100-10

JANUARY 2018