





NOTES: UNLESS OTHERWISE SPECIFIED

- 1. MATERIAL: MATERIAL SPECIFIED AT INDIVIDUAL PART LEVEL
- 2. ALL DIMENSIONS ARE TO THEORETICAL SHARP.
- 3. REMOVE BURRS AND BREAK ALL SHARP EDGES .03 MAX.
- 4. ALL DIMENSIONS ARE IN INCHES UNLESS STATED OTHERWISE.
- 5. PARTS SHALL BE FREE OF GREASE AND CUTTING FLUID.
- 6. POWDER COAT PER MIL-PRF-24712A (TYPE 3, CLASS 3)

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	X1	DEVELOPMENT	03/15/2017	KRH



ISOMETRIC VIEW
FOR REFERENCE ONLY

BOM TABLE			
ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
1	A-FWM	FWM FLANGE	1
2	HFWM-18.00	HORIZONTAL FLOATING WALL MOUNT	1

RELEASED

<p>UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES</p> <p>TOLERANCES ARE:</p> <table border="0"> <tr> <td>.XX ± .01</td> <td>ANGLES</td> </tr> <tr> <td>.XXX ± .005</td> <td>XX° ± 1°</td> </tr> </table>	.XX ± .01	ANGLES	.XXX ± .005	XX° ± 1°	<p>ENGINEER</p> <p>ENGINEER</p> <p>ENGINEER</p> <p>CHECKED CAS 03/15/2017</p> <p>DRAWN KRH 03/15/2017</p> <p>MANAGER APPROVAL</p>	<p>Centerline Brackets</p>
	.XX ± .01	ANGLES				
.XXX ± .005	XX° ± 1°					
<p>INTERPRET DRAWINGS IN ACCORDANCE WITH:</p> <p>ASME Y14.100 ENGINEERING DRAWING PRACTICES</p> <p>ASME Y14.38 ABBREVIATIONS</p> <p>ASME Y14.5 DIMENSIONING AND TOLERANCING</p> <p>ASME Y14.6 SCREW THREAD REPRESENTATION</p> <p>ASME Y14.8 CASTINGS, FORGINGS & MOLDED PARTS</p> <p>AWS A2.4 WELDING SYMBOLS</p> <p>IEEE STD 315 SYMBOLS FOR ELECTRICAL AND ELECTRONIC DIAGRAMS</p>	<p>THE INFORMATION ON THIS DRAWING IS PROPRIETARY AND SHALL NOT BE DISCLOSED, USED, OR DUPLICATED FOR PROCUREMENT OR MANUFACTURING PURPOSES WITHOUT THE EXPRESS WRITTEN CONSENT OF CENTERLINE STEEL, LLC</p> <p>THIRD ANGLE PROJECTION</p>	<p>DRAWING TITLE</p> <p>FLOATING WALL MOUNT BRACKET</p>				
<p>USED ON APPLICATION</p>	<p>SCALE 1:2</p>	<p>SIZE D</p> <p>CAGE CODE</p> <p>DRAWING NO FWM-R18</p> <p>REV X1</p> <p>SHEET 1 OF 1</p>				