

# METALWRAP-H w/MR-100

NOTCH PANEL FACE AT  
CORNERS AS SHOWN  
(PROVIDES A THERMAL  
BREAK)

APPLY A CURING BUTYL SEALANT  
PLUG NEAR EACH PANEL END  
DURING PANEL ERECTION.  
(SEE DETAIL BELOW)

SEALANT BETWEEN  
PANEL LINER AND  
CORNER FLASH

CONTINUOUS  
INTERIOR SIDE  
CORNER  
FLASHING

6" WIDE  
EXTERIOR SIDE  
MEMBRANE OR  
METAL FLASHING;  
CONTINUOUS  
ONTO BASE  
FLASHING BELOW.

INTERIOR  
GYPSUM  
BOARD

MINIMUM SEALANT  
CONTACT SHOWN

FLASHING  
TAPE

SEALANT PLUG DETAIL  
APPLY SEALANT AS  
PANELS ARE ERECTED.

STEEL STUD  
18 GA. MIN.

3/4" HATCH CHANNELS @  
16" O.C, MAX.

PLASTER INSIDE CORNER  
REINFORCEMENT

CONTINUOUS METALWRAP PANEL  
RAIL AT EACH PANEL SIDE  
JOINT (36" O.C.) VERTICALLY  
AND FASTENED INTO EACH  
FRAMING MEMBER (16" TO 24"  
O.C.) HORIZONTALLY

7/8" 3-COAT CEMENT-  
PLASTER O/ GALV.,  
SELF-FURRING METAL  
LATH

METALWRAP PANEL;  
FIELD CUT AS REQ'D