



MODEL #'s 3200, 3220

**TABLE #1
SECTION CHART**

DOOR HEIGHT	NUMBER OF SECTIONS
6'0"	3
6'3" - 6'0"	4
6'3" - 10'0"	5
10'3" - 12'0"	6
12'3" - 14'0"	7
14'3" - 16'0"	8
16'3" - 18'0"	9

NOTE: DOOR HEIGHT IS AVAILABLE IN 3" INCREMENTS

**TABLE #2
PANEL CHART**

DOOR WIDTH	NUMBER OF PANELS
7'0" - 9'2"	2
9'4" - 13'2"	3
13'4" - 16'2"	4
16'4" - 20'2"	5
20'4" - 24'2"	6
24'4" - 26'2" *	7

* FOR 3220 ONLY

NOTE: DOOR WIDTH IS AVAILABLE IN 2" INCREMENTS

**TABLE #3
LITE AVAILABILITY CHART**

WINDOW SIZE	DOOR WIDTH	LITES PER SECTION
8" x 24"	7'0" - 9'2"	2
	9'4" - 13'2"	3
	13'4" - 16'2"	4
	16'4" - 20'2"	5
14" x 28"	20'4" - 24'2"	6
	8'0" - 9'2"	2
	9'4" - 11'0"	3
	11'2" - 13'2"	3
14" x 40"	13'4" - 15'2"	4
	15'4" - 16'2"	4
	8'0" - 9'2"	2
	9'4" - 11'0"	1 (CENTER PANEL)
	11'2" - 13'2"	3
14" x 40"	13'4" - 15'2"	2 (CENTER PANELS)
	15'4" - 16'2"	4

**TABLE #4A
REINFORCEMENT CHART (3200)**

DOOR HEIGHT	DOOR WIDTH			
	UP TO 14'2"	14'4" - 16'2"	16'4" - 18'2"	18'4" - 22'2"
UP TO 6'1"	NONE	3 ea. 2-1/4"	4 ea. 3"	4 ea. 4" C-CHANNEL
6'3" to 10'1"	NONE	3 ea. 2-1/4"	5 ea. 2-1/4"	5 ea. 3"
10'3" to 12'1"	NONE	4 ea. 2-1/4"	6 ea. 2-1/4"	6 ea. 3"
12'3" to 14'1"	NONE	4 ea. 2-1/4"	7 ea. 2-1/4"	7 ea. 3"
14'3" to 16'1"	NONE	5 ea. 2-1/4"	8 ea. 2-1/4"	8 ea. 3"
16'3" to 18'1"	NONE	5 ea. 2-1/4"	9 ea. 2-1/4"	9 ea. 3"

**TABLE #4B
REINFORCEMENT CHART (3220)**

DOOR HEIGHT	DOOR WIDTH			
	UP TO 16'2"	16'4" - 17'2"	17'4" - 18'2"	18'4" - 22'2"
UP TO 6'1"	NONE	3 ea. 2-1/4"	3 ea. 2-1/4"	4 ea. 3"
6'3" to 10'1"	NONE	3 ea. 2-1/4"	5 ea. 2-1/4"	5 ea. 3"
10'3" to 12'1"	NONE	4 ea. 2-1/4"	6 ea. 2-1/4"	6 ea. 3"
12'3" to 14'1"	NONE	4 ea. 2-1/4"	7 ea. 2-1/4"	7 ea. 3"
14'3" to 16'1"	NONE	5 ea. 2-1/4"	8 ea. 2-1/4"	8 ea. 3"
16'3" to 18'1"	NONE	5 ea. 2-1/4"	9 ea. 2-1/4"	9 ea. 3"