



- 78-Spring
- 80-Tread
- 86-Hinge
- 88-Side bracket
- 93-Stile end
- 94-Stringer (ladder side element)

G	S	E
Distance between steps	Steps width	Steps length
[inch]	[inch]	[inch]
9 7/8"	3 3/8"	13 3/4"

LMS	Manufacturer's part number	ATTIC LADDER LMS								
		H	A	B	K	R	C	T	WxL	MxN
		Ceiling height	Width ceiling opening dimensions	Length ceiling opening dimensions	Folded ladder height	Projection	Landing space	Frame height	Outside frame dimensions	Internal box dimensions
		[inch]	[inch]	[inch]	[inch]	[inch]	[inch]	[inch]	[inch]	[inch]
22 1/2"x47	66865	7'2"-8'11"	22 1/2"	47"	10"	65 1/2"	56"	5 1/2"	22"x46 5/8"	20 1/2"x44 7/8"
25"x47	66866		25"	47"					24 1/2"x46 5/8"	23"x44 7/8"
22"x54	66867	22 1/2"	54"	73 1/4"		62 1/4"	22"x53 1/2"		20 1/2"x51 3/4"	
25"x54	66868	25"	54"				24 1/2"x53 1/2"		23"x51 3/4"	
30"x54	66869		30"	54"				29 1/2"x53 1/2"	28 1/2"x51 3/4"	



LMS



Warning! The present drawing is for informational-demonstrative purposes only and as such cannot constitute a basis for performance. All dimensions presented in this drawing should be verified on site. Because of the fact that the drawing is a schematic one, FAKRO shall not assume any responsibility for the actual installation quality. This drawing is FAKRO's property and cannot be published or used publicly without our written consent.

Technical drawing: The LMS Attic Ladder	FORMAT: A4	SCALE: 1:25	DATE: 07.2020
--	---------------	----------------	------------------