

ITEM: LOCK TOGGLE

MATERIAL: TYPE 316 STAINLESS STEEL.

FITTING TYPE: NON-ADJUSTABLE CABLE END FITTING

SWAGE TYPE: MACHINE HEX SWAGE AT FACTORY (ALSO AVAILABLE IN CABLECRIMP HAND SWAGE STYLE FOR ATTACHING IN THE FIELD).

POST TYPE: TUBULAR METAL POSTS ONLY (POSTS NOT INCLUDED).


FASTENING TO POST: PASS THROUGH HOLE IN END/TERMINATION POST AND FITTING AUTOMATICALLY TOGGLES INTO LOCKING POSITION INSIDE POST.

FASTENING AT ANGLES: TOGGLE ACCOMODATES ANGLES WITHOUT DRILLING ANGLED HOLES.

CABLE TENSIONING: NON-ADJUSTABLE FIXED END.

HARDWARE PAIRINGS: USUALLY PAIRED WITH ANOTHER LOCK TOGGLE PLUS AN IN-LINE TURNBUCKLE. MUST BE USED WITH A TENSION ADJUSTMENT FITTING, DO NOT PAIR WITH ANOTHER FIXED END.

SUPPLIER: FEENEY, INC.



LOCK TOGGLE, STAINLESS STEEL

PART#	SWAGE TYPE	CABLE SIZE	LENGTH (L)	BEFORE SWAGE DIA (SBØ)	ATTACHMENT POST DRILL HOLE Ø
3169	MACHINE	1/8"	1-1/2"	1/4"	5/16"
3164	CABLECRIMP	1/8"	1-1/2"	7/32"	5/16"

CableRail Reference Drawing:
LOCK TOGGLE

THIS DRAWING IS THE PROPERTY OF FEENEY INC. ANY REPRODUCTION OF THIS DOCUMENT WITHOUT THE EXPRESSED WRITTEN CONSENT OF FEENEY INC. IS STRICTLY PROHIBITED.

DATE:	05/15/13
PAGE:	1 of 1
REV:	A (12/15/17) MRJ
BY:	DSY
CHK:	BWA

feeney 

2603 Union St., Oakland, CA 94607
P: 800-888-2418 F: 510-893-9484
www.feeneyinc.com