



FRONT VIEW II SCALE 1:2.5

SECTION VIEW A-A II SCALE 1:2.5



DETAIL DW II SCALE 2:1



ISOMETRIC BACK VIEW II SCALE 1:1.5

- NOTES:
- 4" = 24" high letters
  - Typical stud length 2" beyond top of letter
  - Letters under 8" high, 10/24 studs, 8" high and larger, or 1/2" thick or more, 1/4-20 stainless steel studs
  - Minimum 2 studs per letter, min. 3/8" thick
  - Round letters (O, C, G, Q, S) sanded flat tops - optional
  - Tie back recommended if over 8" high letters (not included)
  - Letters or logos, standard or custom



TITLE: FLAT CUT METAL - TOP STUD MOUNT			
MATERIAL: METAL		PRODUCT TYPE: FLAT CUT METAL	
DWG NO. FTMT30	REV 10/25/16	SCALE: AS INDICATED	SHEET 1 OF 1