




"FE-12" STANDARD ACCESSORIES



REQ'D: _____ PCS. @ 1'-0" LG.


"FE-12" INSIDE CLOSURES



**ENLARGED
CROSS SECTION**


REQ'D: _____ LF.

SHEETING SCREWS



#12/14 x 1 1/2" SDWW
REQ'D: _____ PCS.

TRIM SCREWS



1/4-14 x 7/8" SDWW
REQ'D: _____ PCS.

VINYL PANEL SPLINE(GASKET)

STANDARD FASTENERS

NOTES:

1. "FE-12" CLOSURES ARE A CLOSED CELL POLYETHYLENE FACTORY FORMED TO THE PANEL PROFILE AS SHOWN ABOVE.
2. SEALER TAPE IS A NON-DRYING, NON-SKINNING, BUTYL BASE TAPE SUPPLIED IN 3/32" THICK x 1/2" WIDE x 50' ROLLS.
3. FASTENERS ARE ZINC PLATED CARBON STEEL, 5/16" HEX HEAD, SELF DRILLING & SELF TAPPING METAL SCREWS. FASTENERS CAN BE SUPPLIED WITH PAINTED HEADS TO MATCH ROOFING OR SIDING.
4. CONTACT FACTORY FOR PRICE AND AVAILABILITY OF NON-STANDARD ACCESSORIES.



BOX 515 RAILROAD STREET
SANDY LAKE, PENNSYLVANIA 16145-0515
PHONE: 800-245-0396 ° FAX: 724-376-3864

"Fe-12" Concealed Fastener
Panel
Standard Details

DRAWN BY: TRW DATE: 3/2/00
CHECKED BY: CANON DATE: _____

"FE-12" Standard
Accessories

DRAWING NO.
FE12-13