

NOM HEIGHT (A)
3'-0"
3'-6"
4'-0"
5'-0"
6'-0"
7'-0"
8'-0"
CUSTOM HEIGHTS AVAILABLE


POST OPTION (C)
3" SQ X 12 GA
4" SQ X 11 GA
6" SQ X 3/16" WALL
8" SQ X 1/4" WALL
10" SQ X 1/4" WALL

PICKET OPTION (E)	
1" SQ	14 GA
	16 GA
	18 GA

A ____ " NOM HEIGHT
B ____ " FACE TO FACE OF POSTS
C ____ " POST SIZE ____ GAUGE
D ____ " POST LENGTH
E ____ " PICKET SIZE ____ GAUGE

NOTES:

1. INSTALLATION TO BE COMPLETED IN ACCORDANCE WITH MANUFACTURER'S SPECIFICATIONS.
2. DO NOT SCALE DRAWINGS.
3. SPECIFICATIONS SHOWN CAN BE CHANGED ONLY BY THE MANUFACTURER.
4. FOOTING WIDTH TO BE (4) X POST WIDTH.
5. CONTRACTORS NOTE: FOR PRODUCT AND COMPANY INFORMATION VISIT www.CADdetails.com/info REFERENCE NUMBER 2812-120.



GUARDIAN GATE

4 RAIL, DOUBLE SWING GATE, 1 INCH PICKETS, 24 FT. (OR LARGER) OPENING