

- AT 10'-0" (3 m) INTERVALS MAXIMUM, AND 18" (457 mm) HIGH MAXIMUM FOR NON ADHERED MEMBRANE PASTENING REQUIRED SMOOTH CONCRETE WALLS, OR ANY JM APPROVED SUBSTRATE, IE. PLYWOOD, SECUROCK GYPSUM-FIBER AND DENSDECK . SEE DETAIL T-FW-M1 FOR JM APPROVED FASTENING METHODS.
- 2. FOR JM APPROVED BASE FLASHING FASTENING METHODS SEE T-FW-B DETAILS. A SUFFICIENT BACKER FASTENING STRIP MUST BE INSTALLED BEHIND SUBSTRATES DIRECTLY TO STUDS FOR INSTALLATION OF TERMINATION BARS AND FLASHINGS WHEN SUBSTRATES WILL NOT SUPPORT A PROPER, SECURE INSTALLATION. SEE DETAIL T-FW-M2I FOR BACKER DETAIL.
- 3. FOR JM APPROVED TOP OF WALL FLASHING METHODS SEE T-FW-T DETAILS.
- 4. APPROVED EXTERIOR GYPSUM SHEATHING FOR ROOF FLASHING APPLICATION INCLUDE SECUROCK® GYPSUM-FIBER AND DENSEDECK®.

DRAWING NO. T-FW-M2I FLASHING WALL		HIGHWALL FLASHING WITH METAL BACKING STRIP ISOMETRIC VIEW		
		MEMBRANE TYPE: JM TPO	Johns Manville is a manufacturer of commercial roofing products and offers this general conceptual information to you as a courtesy. This complimentary assistance is not to be used or relied upon by anyone as a substitute for professional engineering design and documentation required by building	
SCALE N.T.S	ISSUE DATE 11-06-20	MAXIMUM GUARANTEE TERM: N/A	code, contract, or applicable law. By accepting these comments you agree they do not constitute any representations, endorsements of, or an assumption by Johns Manville of any liability for either the adequacy of the design of this building or any other material not supplied by Johns Manville.	Johns Manville