NOTES:

0811A+

1 1/2" MIN.

CONTINUOUS WELD

IM INSULATION / COVER BOARD

SEE NOTE

- REFER TO JOHNS MANVILLE WEBSITE (www.jm.com) FOR MOST UP-TO-DATE INFORMATION.
- 2. PLEASE SEE THERMOPLASTIC POLYOLEFIN SELF-ADHERED MEMBRANE INSTALLATION GUIDE FOR A FULL DESCRIPTION OF INSTALLATION INSTRUCTIONS AND REQUIREMENTS WHICH ARE CONSIDERED A PART OF THIS DETAIL.
- 3. ANY CARPENTRY OR METAL WORK SHOULD BE DESIGNED AND CONSTRUCTED IN ACCORDANCE WITH LOCAL CODE REQUIREMENTS AND/OR PROJECT SPECIFICATIONS. THESE COMPONENTS SHOULD BE REVIEWED AND APPROVED BY A LICENSED DESIGN PROFESSIONAL. CONTACT JM TECHNICAL FOR METAL OPTIONS TO BE INCLUDED WITHIN THE JM NDL GUARANTEE.
- 4. JM TPO EDGE SEALANT IS REQUIRED ON ALL CUT OR NON-ENCAPSULATED EDGES OF REINFORCED MEMBRANE. THIS INCLUDES FACTORY CUT MEMBRANE (SEE DETAIL T-MS-01).
- 5. FOR JM APPROVED BASE FLASHING FASTENING METHODS SEE DETAILS T-FW-B9, B10, B11, B12. A SUFFICIENT BACKER FASTENING STRIP MUST BE INSTALLED BEHIND SUBSTRATES DIRECTLY TO STUDS FOR INSTALLATION OF TERMINATION BARS AND FLASHINGS WHEN SUBSTRATES WILL NOT SUPPORT A PROPER, SECURE INSTALLATION. SEE DETAIL T-FW-M2I FOR BACKER DETAIL.

JM TPO EDGE SEALANT

(IF REQUIRED) SEE NOTE 4

NOTES CONTINUED:

SEE

WALL/SUBSTRATE

SEE NOTE 10

SEE

NOTE 6

SEE

NOTE

NOTE

- 6. FOR JM APPROVED INTERMEDIATE FLASHING FASTENING METHODS SEE T-FW-I DETAILS. MINIMUM FLASHING TERMINATION HEIGHT IS 8" (203 mm) ABOVE ROOF SURFACE. INTERMEDIATE SELF ADHERED MEMBRANE FASTENING REQUIRED AT 10'-0" (3.048 m) INTERVALS MAXIMUM.
- 7. FOR JM APPROVED TOP OF WALL FLASHING METHODS SEE T-FW-T DETAILS.

JIM SELT AUMENBRANE
JIM SELT AUMENBRANE
TPO FLASHING

8. JM TPO REINFORCED TERMINATION STRIP (RTS) IS NOT ACCEPTABLE FOR USE WITH JM SELF ADHERED TPO MEMBRANE.

JM APPROVED **FASTENERS**

AND PLATES 12" O.C. MAX.

- 9. ALWAYS PRIME POROUS SURFACES WITH JM SA PRIMER OR JM SA LVOC PRIMER PRIOR TO INSTALLING JM TPO SA FLASHING MEMBRANE. PRIME SMOOTH SURFACES WITH JM SA PRIMER OR JM SA LVOC PRIMER WHEN TEMPERATURES ARE BETWEEN 20° F AND 40° F. JM SELF ADHERED TPO MEMBRANE IS NOT TO BE INSTALLED WHEN TEMPERATURE IS BELOW 20 DEGREES.
- 10. APPROVED SUBSTRATES FOR THE APPLICATION OF JM TPO-SA FLASHING MEMBRANE ARE GYPSUM, CONCRETE, FIBER CEMENT AND WOOD.

SELF ADHERED TPO BASE & WALL FLASHING WITH COPING ISOMETRIC VIEW

T-FW-M3T

MEMBRANE TYPE: JM SELF ADHERED TPO

FLASHING WALL

SCALE

N.T.S

ISSUE DATE 03-22-19

MAXIMUM GUARANTEE TERM: N/A

Johns Manville is a manufacturer of commercial roofing products and offers this general conceptual information to you as a courtesy. This complimentary assistance is not to be used or relied upon by anyone as a substitute for professional engineering design and documentation required by building code, contract, or applicable law. By accepting these comments you agree they do not constitute any representations, endorsements of, or an assumption by Johns Manville of any liability for either the adequacy of the design of this building or any other material not supplied by Johns Manville.



DRAWING NO.