

## NOTES CONTINUED:

- 6.FOR JM APPROVED INTERMEDIATE FLASHING FASTENING METHODS SEE T-FW-I DETAILS. MINIMUM FLASHING TERMINATION HEIGHT IS 8" (203 mm) ABOVE ROOF SURFACE, WHEN ADHERING JM TPO MEMBRANES VERTICALLY ON A SUBSTRATE, INTERMEDIATE MEMBRANE FASTENING IS REQUIRED AT 10'-0" (3.048 m) INTERVALS MAXIMUM.
- 7. FOR JM APPROVED TOP OF WALL FLASHING METHODS SEE T-FW-T DETAILS.
- 8. JM APPROVED ADHESIVES FOR USE ON VERTICAL FLASHING APPLICATIONS INCLUDES JM LVOC MEMBRANE ADHESIVE (TPO & EPDM), JM MEMBRANE BONDING ADHESIVE (TPO & EPDM) AND JM TPO WATER BASED MEMBRANE ADHESIVE.

T-FW-M4I FLASHING WALL		TPO BASE & WALL FLASHING WITH COPING ISOMETRIC VIEW		
		MEMBRANE TYPE: JM TPO	Johns Manville is a manufacturer of commercial roofing products and offers this general conceptual information to you as a courtesy. This complimentary assistance is not to be used or relied upon by anyone as a substitute for professional engineering design and documentation required by building	
SCALE N.T.S	1SSUE DATE 03-22-19	MAXIMUM GUARANTEE TERM: N/A	code, contract, or applicable law. By accepting these comments you agree they do not constitute any representations, endorsements of, or an assumption by Johns Manville of any liability for either the adequacy of the design of this building or any other material not supplied by Johns Manville.	Johns Manvil

