





Hotdip Galvanized: ASTM A
153 Class B-2: (1.50 oz/
ft².) (0.46kg/m²)



304 STAINLESS STEEL
ASTM A 167, ASTM A 666,
ASTM A 240/A240M
AISI Type 304

Heckmann Building Products
Division of Mechanical Plastics Corp.
110 Richards Avenue
Norwalk, CT 06854-1685 USA

304 STAINLESS STEEL
ASTM A 167, ASTM A 666,
ASTM A 240/A240M
AISI Type 304

Hotdip Galvanized: ASTM A
153 Class B-2: (1.50 oz/
ft²)(0.46kg/m²)


#130 Weld-On Channel Slot
Shown on I-Beam with

#129 Channel Slot Triangular Wire Tie -In Mortar Joint of CMU Block

#130 - 11GA & 16GA 304 StainLess Steel
12GA Hot-Dip Galv.

#129 Wire-Tie - 3/16 ϕ with 12GA Clip
Stainless Steel and Hot-Dip Galv

Lengths: 3" 4" 5" 6" 7" 9" (from face of channel)



#129-Wire Tie

#130 -Weld-On
Channel Slot

