



Cat No.	Swage Type	Cable Size	Thread size	Body Length (B)	Open Length (L)	Closed Length (L)
19-314-10B	Machine	1/8"	1/4" - 28	4-1/2"	11-1/4"	8-1/4"
19-316-10B	Machine	3/16"	1/4" - 28	4-1/2"	11-1/4"	8-1/4"
19-308-7B	Machine	1/4"	5/16" - 24	5-1/8"	14-1/4"	10-1/4"
26-412-10B	Hand Crimp	1/8"	1/4" - 28	4-1/2"	11-11/16"	8-1/8"
27-412-10B	Hand Crimp	3/16"	1/4" - 28	4-1/2"	12"	8-1/2"

JOHNSON ARCHITECTUAL REFERENCE DRAWING:

## Classic Ball End Turnbuckle

THIS DRAWING IS THE PROPERTY OF C. SHERMAN JOHNSON CO. INC. ANY REPRODUCTION OF THIS DOCUMENT WITHOUT THE EXPRESSED WRITTEN CONSENT OF C. SHERMAN JOHNSON CO. INC. IS STRICTLY PROHIBITED.

DRAWING No.

MATERIAL

MANUFACTURE

BY

DATE

CBETB-01

Type 316 Stainless Steel

C. Sherman Johnson Co., Inc.

SBG

7/28/23

EAST HADDAM, CT 06423  
TEL 1-800-874-7455  
csjohnson.com