



Cat No.	Swage Type	Cable Size	Thread Size	Thread Length (T)	Terminal Length (L)
25-500	Machine	1/8"	1/4" - 28	2-1/2"	6-1/4"
25-500-L	Machine	1/8"	1/4" - 28	2-1/2"	8-5/8"
25-502	Machine	3/16"	1/4" - 28	2-1/2"	6-1/4"
25-502-L	Machine	3/16"	1/4" - 28	2-1/2"	8-5/8"
25-504-3	Machine	1/4"	5/16" - 24	3"	5-3/4"
25-504-6	Machine	1/4"	5/16" - 24	6"	8-1/2"
26-500	Hand Crimp	1/8"	1/4" - 28	2-1/2"	6-1/4"
26-500-L	Hand Crimp	1/8"	1/4" - 28	2-1/2"	8-5/8"
27-500	Hand Crimp	3/16"	1/4" - 28	2-1/2"	6-1/4"
27-500-L	Hand Crimp	3/16"	1/4" - 28	2-1/2"	8-5/8"

JOHNSON ARCHITECTURAL REFERENCE DRAWING:

Smooth Line Threaded Terminal

THIS DRAWING IS THE PROPERTY OF C. SHERMAN JOHNSON CO. INC. ANY REPRODUCTION OF THIS DOCUMENT WITHOUT THE EXPRESSED WRITTEN CONSENT OF C. SHERMAN JOHNSON CO. INC. IS STRICTLY PROHIBITED.

DRAWING No.

MATERIAL

MANUFACTURE

BY

DATE

SLTT-01

Type 316 Stainless Steel

C. Sherman Johnson Co., Inc.

SBG

7/31/23

EAST HADDAM, CT 06423
TEL 1-800-874-7455
csjohnson.com