



				A	B	C	D	E	Weight	
Cat. No.	Type	Approx. Breaking strength	Safe Working Load	Length Open	Length Closed	Thread Size	Eye ID	Body Length	Lb.	oz.
03-155	Eye/Eye	1,000 lbs.	400 lbs.	8-1/2"	6"	10-32	5/16"	3-1/2"		3
04-155	Eye/Eye	2,500 lbs.	1,000 lbs.	10"	7"	1/4-28	3/8"	4-1/2"		5
05-155	Eye/Eye	4,000 lbs.	1,600 lbs.	11-1/4"	8-1/2"	5/16-24	1/2"	5-1/8"		8
06-155	Eye/Eye	7,000 lbs.	2,800 lbs.	12-3/4"	8-3/4"	3/8-24	5/8"	5-3/8"		14
09-155	Eye/Eye	10,500 lbs.	4,200 lbs.	15-1/4"	10-1/2"	1/2-20	3/4"	7"	2	0
10-155	Eye/Eye	14,800 lbs.	5,900 lbs.	17-3/4"	12-3/4"	5/8-18	7/8"	8-5/8"	4	0

Note: Welded Eye

JOHNSON ARCHITECTUAL REFERENCE DRAWING:

Eye-to-Eye Stainless T-316 Tubular Turnbuckle

THIS DRAWING IS THE PROPERTY OF C. SHERMAN JOHNSON CO. INC. ANY REPRODUCTION OF THIS DOCUMENT WITHOUT THE EXPRESSED WRITTEN CONSENT OF C. SHERMAN JOHNSON CO. INC. IS STRICTLY PROHIBITED.

DRAWING No.

MATERIAL

MANUFACTURE

BY

DATE

EESTTT-01

Type 316 Stainless Steel

C. Sherman Johnson Co., Inc.

SBG

7/31/23



Johnson
Industrial Hardware

C. Sherman Johnson Co., Inc.

EAST HADDAM, CT 06423
TEL 1-800-874-7455
csjohnson.com