




## KALWALL 2 3/4" [70mm] DRAINABLE LOUVER



1. **SPECIFICATIONS**  
8063-T8 EXTRUDED ALUM  
ALL WELDED CONSTRUCTION
2. **FINISH**  
MILL, KRF OR ANODIZED
3. **SCREENS/BLANK OFF PLATE**  
(A) BIRD SCREENS  
3/4" [19mm] FLAT. EXPANDED  
ALUM. .051" [1.3mm THICK]  
(B) INSECT SCREENS  
18 X 16 ALUMINUM MESH  
(C) .063 ALUM BLANK OFF PLATE
4. **DIMENSIONS** NOTE: RECTANGULAR ONLY  
WIDTH: MIN. 10" [254mm]  
MAX. 60" [1524mm]  
HEIGHT: MIN. 6 1/8" [158mm]  
MAX. 96" [2438mm]  
BLADES SPACING: 2 1/16" [52mm] NOM.
5. **FREE AREA**  
48" [1219mm] W x 48" [1219mm] H 6.38 ft<sup>2</sup> [593 m<sup>2</sup>], 40%  
BEGINNING POINT OF WATER PENETRATION  
1,229.6 ft<sup>3</sup> (m [7,845 ft<sup>3</sup>]/min [2391 m<sup>3</sup>/min (34.82 m<sup>3</sup>/min)])
7. **PRESSURE DROP**

|     | H <sub>2</sub> O | f/min   | f <sup>3</sup> /min | m/min  | m <sup>3</sup> /min |
|-----|------------------|---------|---------------------|--------|---------------------|
| IN  | .612"/15.54mm    | 2,000.3 | 12,762              | 609.69 | 361.4               |
|     | .051"/1.29mm     | 571     | 3,643               | 174    | 103.2               |
| OUT | .439"/11.15mm    | 2,000.5 | 12,763              | 609.75 | 361.4               |
|     | .051"/1.29mm     | 680.2   | 4,340               | 207.32 | 122.9               |



**KALWALL®**  
high performance translucent building systems

**Facades • Window Replacement • Drainable Louver**