

## NOTES CONTINUED:

- 6. FOR JM APPROVED INTERMEDIATE FLASHING FASTENING METHODS SEE P-FW-I DETAILS. MINIMUM FLASHING TERMINATION HEIGHT IS 8" (203 m) ABOVE ROOF SURFACE. INTERMEDIATE FASTENING REQUIRED 18" (457 m) HIGH MAXIMUM FOR NON ADHERED MEMBRANE ON CMU, BRICK, SMOOTH CONCRETE WALLS, OR ANY JM APPROVED SUBSTRATE, IE. PLYWOOD, SECUROCK GYPSUM-FIBER AND DENSDECK. SEE DETAIL P-FW-M2I FOR JM APPROVED FASTENING METHODS.
- 7. FOR JM APPROVED TOP OF WALL FLASHING METHODS SEE P-FW-T DETAILS.
- 8. JM APPROVED ADHESIVES FOR USE ON VERTICAL FLASHING APPLICATIONS INCLUDES JM PVC MEMBRANE ADHESIVES (LOW VOC ONLY).

Ib-LM-MITTH			PVC BASE & WALL FLASHING WITH COPING ISOMETRIC VIEW		
			MEMBRANE TYPE: JM PVC	Johns Manville is a manufacturer of commercial roofing products and offers this general concep information to you as a courtesy. This complimentary assistance is not to be used or relied upor anyone as a substitute for professional engineering design and documentation required by build	
	SCALE N.T.S	ISSUE DATE 03-22-19	MAXIMUM GUARANTEE TERM: N/A	code, contract, or applicable law. By accepting these comments you agree they do not constitute any representations, endorsements of, or an assumption by Johns Manville of any flability for either the adequacy of the design of this building or any other material not supplied by Johns Manville.	   Jo

