


F1100-C-N

SCALE 1 : 4

STRAINER DIAMETER	STRAINER ADJUSTMENT		ANSI/ASME RATING		PIPE SIZE	NO HUB	BODY HEIGHT PUSH IN (P)	THREADED (T)	INSIDE CAULK (X)	PVC/ABS (-30/-31)
	MIN	MAX	FREE AREA SQ IN	LOAD RATING NB(-1) SS(-3)						
7"(178)	2.81"(71)	3.81"(97)	11 SQ IN	5000 TO 7499 LBS	2"(51)	2.75"(70)	3.375"(86)	2.25"(57)	3.75"(95)	2.94"(75)
					3"(76)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
					4"(102)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
9"(229)	2.81"(71)	3.81"(97)	18 SQ IN	7499 LBS	5"(127)	2.75"(70)	—	2.625"(67)	3.75"(95)	—
					6"(152)	3.25"(83)	4.75"(121)	—	—	—

MIFAB

FOR CATALOGUE USE ONLY



SCALE : 1 : 4

in/[mm]

GENERAL TOLERANCE :
 LINEAR : N/A
 ANGULAR : N/A
 UNLESS OTHERWISE SPECIFIED

P/N :

F1100-C-N

SHEET : 1 OF 1

A5

REV :

0