


C1100-US
SCALE 1 : 4

SQUARE TOP ASSEMBLY	TOP ASSEMBLY ADJUSTMENT		ANSI/ASME LOAD RATING	PIPE SIZE	NO HUB	PUSH DN(P)	BODdy HEIGHT THREADED (T)	INSIDE CAULK (X)	PVC/ABS (-30/-31)
	MIN	MAX							
5"(127) X 5"(127)	0.5"(13)	1.25"(32)	2000 TO 4.999LBS NB(-1)	2"(51)	2.75"(70)	3.375"(86)	2.25"(57)	3.75"(95)	2.94"(75)
			5000 TO 7499LBS SS(-3)	3"(76)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
				4"(102)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
				5"(127)	3.25"(83)	—	2.625"(67)	3.75"(95)	—
			6"(152)	3.25"(83)	—	—	—	—	

MIFAB

FOR CATALOGUE USE ONLY



SCALE : 1 : 4

in/[mm]

GENERAL TOLERANCE :
LINEAR : N/A
ANGULAR : N/A
UNLESS OTHERWISE SPECIFIED

P/N :

C1100-US

SHEET : 1 OF 1

A5

REV :

0