

- 5. FOR JM APPROVED BASE FLASHING FASTENING METHODS SEE T-FW-B DETAILS. APPROPRIATE SUBSTRATES FOR VERTICAL RHINOBOND APPLICATION INCLUDES PLYWOOD, OSB, METAL STUD WALLS WITH APPROVED SHEATHING.
- 6. FOR JM APPROVED TOP OF WALL FLASHING METHODS SEE T-FW-T DETAILS.
- 7. TPO MEMBRANE IS SECURED TO RHINOPLATES USING THE INDUCTION WELDER. SEE THE TPO RHINOPLATE SYSTEM APPLICATION GUIDE FOR FURTHER INFORMATION.
- 8. TPO RHINOPLATE APPLICATION IS ONLY APPROVED FOR 60 MIL OR THICKER MEMBRANES.

T-FW-M6I		TPO RHINOBOND WALL FLASHING ISOMETRIC VIEW	
NEW DETA	AIL	MEMBRANE TYPE: JM TPO	Johns Manville is a manufacturer of commercial roofing products and offers this general conceptual information to you as a courtesy. This complimentary assistance is not to be used or relied upon by anyone as a substitute for professional engineering design and documentation required by building
SCALE N.T.S		MAXIMUM GUARANTEE TERM: N/A	code, contract, or applicable law. By accepting these comments you agree they do not constitute any representations, endorsements of, or an assumption by Johns Manville of any liability for either the adequacy of the design of this building or any other material not supplied by Johns Manville.

