

- 6. FOR JM APPROVED INTERMEDIATE FLASHING FASTENING METHODS SEE T-FW-I DETAILS. MINIMUM FLASHING TERMINATION HEIGHT IS 8" ABOVE ROOF SURFACE. INTERMEDIATE ADHERED MEMBRANE FASTENING REQUIRED AT 5'-0" INTERVALS MAXIMUM, AND 18" HIGH MAXIMUM FOR NON ADHERED MEMBRANE ON CMU, BRICK, SMOOTH CONCRETE WALLS, OR ANY JM APPROVED SUBSTRATE, IE. PLYWOOD, GLASS FACED GYPSUM OR JM INVINSA. SEE DETAIL TH-FW-M2I FOR JM APPROVED FASTENING METHODS.
- 7. FOR JM APPROVED TOP OF WALL FLASHING METHODS SEE T-FW-T DETAILS.
- 8. JM APPROVED ADHESIVES FOR USE ON VERTICAL FLASHING APPLICATIONS INCLUDES JM TPO MEMBRANE ADHESIVES (LOW VOC ONLY).
- 9. JM APPROVED ADHESIVES FOR JM TPO FLEECE BACKED MEMBRANE ADHERED OVER BITUMINOUS PLIES INCLUDES HOT ASPHALT, RSUA OR 2P UIA CANISTER.
- 10. JM BITUMINOUS PLIES INCLUDE APPROPRIATE SMOOTH SBS MODIFIED BITUMEN SHEETS APPLIED WITH HOT ASPHALT, MBR COLD APPLICATION ADHESIVE, OR HEAT WELDED TECHNIQUES, AND/OR PLY FELTS APPLIED IN HOT ASPHALT.

TH-FW-M11 TPO HYBRID BASE & WALL FLASHING WITH COPING ISOMETRIC VIEW MEMBRANE TYPE: JM TPO FLEECE BACK HYBRID SCALE N.T.S ISSUE DATE N.T.S MAXIMUM GUARANTEE TERM: 20 YEAR TPO HYBRID BASE & WALL FLASHING WITH COPING ISOMETRIC VIEW Johns Manville is a manufacturer of commercial roofing products and offers this general conceptual information to you as a courtesy. This complimentary assistance is not to be used or relied upon by any one as a substitute for professional engineering design and documentation required by building ocde, contract, or applicable law. By accepting these comments you agree they do not constitute any representations, endorsements of, or an assumption by Johns Manville or either the adequacy of the design of this building or any other material not supplied by Johns Manville. Johns Manville