



NOTES:

- GE ELEMEX 5000 LIQUID FLASHING MAY BE INSTALLED BEFORE OR AFTER THE APPLICATION OF GE ELEMEX 2600 AWB. WHEN INSTALLING BEFORE, THE CUT EDGES OF GYPSUM SHEATHING MAY NEED TO BE COATED WITH GE ELEMEX 2600 AWB.
- ENSURE GE ELEMEX 2600 AWB IS DRY TO THE TOUCH PRIOR TO THE APPLICATION OF GE ELEMEX 5000 LIQUID FLASHING.
- INSIDE CORNER: A PROPERLY CONFIGURED FILLET BEAD OF GE ELEMEX 5000 LIQUID FLASHING MAY BE UTILIZED TO TREAT CHANGE IN SUBSTRATE AT INSIDE CORNERS WITH GAPS < 1/2" (13 MM). THE USE OF BACKER ROD MAY BE REQUIRED. ENSURE A MINIMUM 1/4" (6 MM) - 3/8" (10 MM) ADHESIVE CONTACT TO BOTH SIDES.
- OUTSIDE CORNER: APPLY GE ELEMEX 5000 LIQUID FLASHING TO THE CORNER AT A NOMINAL 20-40 MILS (508-1016 μ) THICKNESS. SPREAD/TROWEL THE GE ELEMEX 5000 LIQUID FLASHING TO A MINIMUM OF 3" (75 MM) ONTO EACH SIDE WALL.
- SEE GE ELEMEX 2600 AWB DATA SHEET FOR LIST OF ADDITIONAL ACCEPTABLE GE SEALANTS/LIQUID FLASHING.

**INSIDE / OUTSIDE CORNERS - METHOD A: GE ELEMEX 5000 LIQUID FLASHING
GE ELEMEX® 2600 AIR AND WATER-RESISTIVE BARRIER SYSTEM**

DETAIL #: AWB-18

THE ABOVE DETAIL IS FOR ILLUSTRATION PURPOSES ONLY. IT IS INTENDED AS A GUIDELINE TO ASSIST MOMENTIVE PRODUCT USERS IN DEVELOPING PROJECT SPECIFIC DETAILS. CONSULT APPROPRIATE SPECIFICATION DOCUMENTS, DATA SHEETS, BUILDING CODES AND ANY OTHER INFORMATION DEEMED NECESSARY FOR SPECIFIC REQUIREMENTS. MOMENTIVE PRODUCT USERS ARE RESPONSIBLE FOR DETERMINING THE SUITABILITY OF MOMENTIVE PRODUCTS FOR THE PARTICULAR APPLICATION AND ALL RELATED PROJECT DETAILS. MOMENTIVE MAKES NO WARRANTY, EXPRESS OR IMPLIED, WITH RESPECT TO THE PERFORMANCE, SUITABILITY OR FITNESS FOR INTENDED USE OF ITS PRODUCTS IN ANY USER'S APPLICATION. ANY SALE OF PRODUCTS OR DELIVERY OF CUSTOMER SUPPORT AND ADVICE BY MOMENTIVE PERFORMANCE MATERIALS INC. AND/OR ANY OF ITS AFFILIATES ("MOMENTIVE") IS MADE EXCLUSIVELY UNDER MOMENTIVE'S STANDARD CONDITIONS OF SALE, WHICH ARE AVAILABLE AT WWW.GE.COM/SILICONES.

SCALE: N.T.S.

DATE: 2017-03-27