



Cat No.	Swage Type	Cable Size	Thread size	Body Length (B)	Open Length (L)	Closed Length (L)
19-314-10F	Machine	1/8"	1/4" - 28	4-1/2"	11-1/2"	8-1/4"
19-316-10F	Machine	3/16"	1/4" - 28	4-1/2"	11-1/2"	8-1/4"
19-308-7F	Machine	1/4"	5/16" - 24	5-1/8"	14-1/4"	10-1/2"
26-412-10F	Hand Crimp	1/8"	1/4" - 28	4-1/2"	11-11/16"	8-1/8"
27-412-10F	Hand Crimp	3/16"	1/4" - 28	4-1/2"	12"	8-1/2"

JOHNSON ARCHITECTUAL REFERENCE DRAWING:

Classic Button Turnbuckle

THIS DRAWING IS THE PROPERTY OF C. SHERMAN JOHNSON CO. INC. ANY REPRODUCTION OF THIS DOCUMENT WITHOUT THE EXPRESSED WRITTEN CONSENT OF C. SHERMAN JOHNSON CO. INC. IS STRICTLY PROHIBITED.

DRAWING No.

MATERIAL

MANUFACTURE

BY

DATE

CBNTB-01

Type 316 Stainless Steel

C. Sherman Johnson Co., Inc.

SBG

7/28/23

EAST HADDAM, CT 06423

TEL 1-800-874-7455

csjohnson.com