

Boral Steel® Architectural Details are divided into three (3) categories based on the install method used:

Architectural details provided for Boral Steel® customers only

BATTEN (Panel is exposed fastened & mounted onto a wood 2x2 batten or steel hat channel)

DIRECT (Panel is exposed fastened & mounted Direct-to-the roof-deck)

GRANITE-RIDGE Shingle (Panel is hidden fastened & mounted Direct-to-the roof-deck)


Battens: Nominal 2"x2" spruce pine fir #2 or better.

Fastener number, spacing and size as per fastener chart.

Install using appropriate Boral Steel "Batten Spacers".

16d Corrosion Resistant Nail or Corrosion Resistant Screw of sufficient length to penetrate rafter/truss by a minimum of 1", maximum 24" on center spacing.

Roofing Underlayment: Wrap minimum 1" over finish edges.



Batten Spacing

PINE-CREST Shake: 14 ¹/₄"

PACIFIC Tile; 14 ¹/₄"

BARREL-VAULT Tile: 14"

Profiles:

PINE-CREST Shake

BARREL-VAULT Tile

PACIFIC Tile

**BATTEN
Fastening**

Boral Steel Stone Coated Roofing
7575 Irvine Ctr Dr Suite 100, Irvine, CA 92618

Drawings
are not to
scale