



Cat No.	Swage Type	Cable Size	Thread size	Body Length (B)	Open Length (L)	Closed Length (L)	Hole Separation (C)
19-314-1T	Machine	1/8"	1/4" - 28	4-1/2"	10-3/4"	7-3/4"	1-3/8"
19-316-1T	Machine	3/16"	1/4" - 28	4-1/2"	11-1/4"	8-1/4"	1-3/8"
19-318-1T	Machine	1/4"	5/16" - 24	5-1/8"	12"	9"	1-1/2"
26-412-1T	Hand Crimp	1/8"	1/4" - 28	4-1/2"	11-1/2"	8-1/2"	1-3/8"
27-412-1T	Hand Crimp	3/16"	1/4" - 28	4-1/2"	11-1/2"	8-1/2"	1-3/8"

JOHNSON ARCHITECTUAL REFERENCE DRAWING:

Classic Deck Toggle Turnbuckle

THIS DRAWING IS THE PROPERTY OF C. SHERMAN JOHNSON CO. INC. ANY REPRODUCTION OF THIS DOCUMENT WITHOUT THE EXPRESSED WRITTEN CONSENT OF C. SHERMAN JOHNSON CO. INC. IS STRICTLY PROHIBITED.

DRAWING No.

MATERIAL

MANUFACTURE

BY

DATE

CDTTB-01

Type 316 Stainless Steel

C. Sherman Johnson Co., Inc.

SBG

7/28/23

EAST HADDAM, CT 06423
TEL 1-800-874-7455
csjohnson.com