

Boral Steel® Architectural Details are divided into three (3) categories based on the install method used:

BATTEN (Panel is exposed fastened & mounted onto a wood 2x2 batten or steel hat channel)

DIRECT (Panel is exposed fastened & mounted Direct-to-the roof-deck)

GRANITE-RIDGE Shingle (Panel is hidden fastened & mounted Direct-to-the roof-deck)


Architectural details provided for Boral Steel® customers only

***Batten Fasteners omitted for clarity.
See fastening drawings for panel and batten attachment.**

Battens: to be nominal 2"x2" spruce pine fir #2 or better fastened to counter battens. Fastener number, spacing and size as per fastener chart. Install using appropriate Boral Steel "Batten Spacers". Top batten space may be "Short".

CAP Mission: Fasten at sides.

Panels: Bend and cut top course "Short Course" as needed to fit batten lay-out.



Batten Spacing


PINE-CREST Shake: 14 1/4"

PACIFIC Tile: 14 1/4"

BARREL-VAULT Tile: 14"

Counter Battens: to be nominal 1"x4" spruce pine fir #2 or better fastened to structural framing. 24" O.C. Max. Fastener number, spacing and size as per fastener chart.

CAP Shake: Fasten at sides. Seal and chip exposed screw.



Profiles:

PINE-CREST Shake

BARREL-VAULT Tile

PACIFIC Tile

**BATTEN
Counter Batten Non-Vented
Ridge**

Boral Steel Stone Coated Roofing
7575 Irvine Ctr Dr Suite 100, Irvine, CA 92618

Drawings
are not to
scale