



Cat No.	Swage Type	Cable Size	Thread size	Body Length (B)	Open Length (L)	Closed Length (L)
19-314	Machine	1/8"	1/4" - 28	4-1/2"	11-1/4"	8-1/4"
19-316	Machine	3/16"	1/4" - 28	4-1/2"	11-1/4"	8-1/4"
19-318-7	Machine	1/4"	5/16" - 24	5-1/8"	12-3/4"	9"
19-308	Machine	1/4"	3/8" - 24	5-3/8"	14-1/4"	10"
26-412	Hand Crimp	1/8"	1/4" - 28	4-1/2"	11-5/8"	8-3/4"
27-412	Hand Crimp	3/16"	1/4" - 28	4-1/2"	11-5/8"	8-3/4"

JOHNSON ARCHITECTUAL REFERENCE DRAWING:

## Classic Jaw Toggle Turnbuckle

THIS DRAWING IS THE PROPERTY OF C. SHERMAN JOHNSON CO. INC. ANY REPRODUCTION OF THIS DOCUMENT WITHOUT THE EXPRESSED WRITTEN CONSENT OF C. SHERMAN JOHNSON CO. INC. IS STRICTLY PROHIBITED.

DRAWING No.

MATERIAL

MANUFACTURE

BY

DATE

CJTTB-01

Type 316 Stainless Steel

C. Sherman Johnson Co., Inc.

SBG

7/28/23

EAST HADDAM, CT 06423  
TEL 1-800-874-7455  
csjohnson.com