



Cat No.	Swage Type	Cable Size	Thread size	Body Length (B)	Open Length (L)	Closed Length (L)
19-314-3	Machine	1/8"	1/4" - 28	4-1/2"	11-3/4"	8-3/4"
19-316-6	Machine	3/16"	1/4" - 28	4-1/2"	11-3/4"	8-3/4"
19-318-27	Machine	1/4"	5/16" - 24	5-1/8"	13-1/4"	9-3/4"
19-308-2	Machine	1/4"	3/8" - 24	5-3/8"	14-7/8"	10-5/8"
26-412-3	Hand Crimp	1/8"	1/4" - 28	4-1/2"	12-1/2"	9-1/2"
27-412-6	Hand Crimp	3/16"	1/4" - 28	4-1/2"	12-1/2"	9-1/2"

JOHNSON ARCHITECTUAL REFERENCE DRAWING:
Classic Swage to Swage Turnbuckle

THIS DRAWING IS THE PROPERTY OF C. SHERMAN JOHNSON CO. INC. ANY REPRODUCTION OF THIS DOCUMENT WITHOUT THE EXPRESSED WRITTEN CONSENT OF C. SHERMAN JOHNSON CO. INC. IS STRICTLY PROHIBITED.

DRAWING No.

MATERIAL

MANUFACTURE

BY

DATE

CSSTB-01

Type 316 Stainless Steel

C. Sherman Johnson Co., Inc.

SBG

7/28/23

EAST HADDAM, CT 06423
 TEL 1-800-874-7455
 csjohnson.com