


RAKE FLASHING - COUNTER BATTEN SYSTEM (Where Required)

MC-19A



Notes:

1. One layer of No. 30 asphalt-saturated felt complying with ASTM D-226 (ASTM D4869 Type IV) or approved equal as a minimum underlayment on all tile roof applications. Other underlayments as approved by local building officials will be allowed.
2. Sheet metal Flashing shall be a minimum of 26 ga. G-90 galvanized steel, 16 oz. copper or an equivalent longevity non-corrosive metal.
3. For tile fastening schedule see Fastening Table 1A and 1B.
4. Dimensions shown are minimums and are intended to be approximate to allow for reasonable tolerances due to field conditions.
5. Rake flashing and wood nailer/trim board shall be raised above the roof deck to a height greater than the height of the installed roof tile.

Drawing shown depicts the application of a generic roof tile installation. Unless otherwise noted it would apply to either concrete or clay tiles.