



Cat. No.	Type	Safe Working Load	A Length Open	B Length Closed	C Thread Size	E Body Length	I Hook Opening	Weight Lb.	oz.
03-655	Hook/Hook	85 lbs.	9"	6-1/2"	10-32	3-1/2"	1/4"		3
04-655	Hook/Hook	195 lbs.	10-1/2"	7-1/2"	1/4-28	4-1/2"	3/8"		5
05-655	Hook/Hook	290 lbs.	11-3/4"	9"	5/16-24	5-1/8"	1/2"		8
06-655	Hook/Hook	405 lbs.	13-1/2"	9-3/4"	3/8-24	5-3/8"	5/8"		14
09-655	Hook/Hook	770 lbs.	15-3/4"	11"	1/2-20	7"	3/4"	2	0
10-655	Hook/Hook	1,235 lbs.	18-1/2"	13-1/2"	5/8-18	8-5/8"	7/8"	4	0

Note: Wireformed Hook

JOHNSON ARCHITECTUAL REFERENCE DRAWING:

Hook-to-Hook Stainless T-316 Tubular Turnbuckle

THIS DRAWING IS THE PROPERTY OF C. SHERMAN JOHNSON CO. INC. ANY REPRODUCTION OF THIS DOCUMENT WITHOUT THE EXPRESSED WRITTEN CONSENT OF C. SHERMAN JOHNSON CO. INC. IS STRICTLY PROHIBITED.

DRAWING No.

MATERIAL

MANUFACTURE

BY

DATE

HHSTTT-01

Type 316 Stainless Steel

C. Sherman Johnson Co., Inc.

SBG

7/31/23



EAST HADDAM, CT 06423
TEL 1-800-874-7455
csjohnson.com