



8" MINIMUM

30-45°

2"

12" MIN.

2"

5"

5"

1-1/2" MAX.

- ANGLED RESIN FILL TYPICAL @ ALL MEMBRANE TERMINATION POINTS.
- CUT-IN REGLET 1" MIN. DEEP, APPLY APPROVED CAULKING AS REQUIRED.
- PREPARE, LEVEL & PATCH SUBSTRATE AS REQUIRED W/APPROVED LEVELING COMPOUND PRIOR TO APPLICATION OF KEMPEROL PRIMER & MEMBRANE (TYP.)
- (2) PLY KEMPEROL MEMBRANE FLASHING EXTEND TOP PLY 12" MIN. HORIZONTALLY ONTO MODIFIED BITUMEN MEMBRANE.
- APPROVED CONTINUOUS CLOSED-CELL POLYETHYLENE BACKER ROD
- CONTINUOUS BOTTOM PLY OF KEMPEROL MEMBRANE @ WALL TO DECK TRANSITION
- CAP SHEET SET IN ADHESIVE OR HEAT WELDED
- BASE SHEET SET IN ADHESIVE OR HEAT WELDED
- APPROVED SUBSTRATE
- APPROVED COMPRESSIBLE FILLER (AS REQUIRED)

DRAWING NO.

KDJ-1A

**HORIZONTAL TO VERTICAL TRANSITION
EXPANSION JOINT W/ CUT-IN REGLET**

REVISION
12-11-15

ISSUE DATE
04-15-08

SCALE
N.T.S.

DRAWN BY
K.S.A.

