


F1100-C-SD

SCALE 1 : 4

STRAINER SQUARE	STRAINER ADJUSTMENT		ANSI/ASME RATING		PIPE SIZE	NO HUB	BODY HEIGHT PUSH ON (P)	THREADED (T)	INSIDE CAULK (X)	PVC/ABS (-30/-31)
	MIN	MAX	FREE AREA SQ IN	LOAD RATING SS(-3)						
6" (152) X 6" (152)	2.38" (60)	3.1" (78)	12 SQ IN	5000 LBS TO 7499 LBS	2" (51)	2.75" (70)	3.375" (86)	2.25" (57)	3.75" (95)	2.94" (75)
					3" (76)	2.75" (70)	3.375" (86)	2.625" (67)	3.75" (95)	3.75" (95)
					4" (102)	2.75" (70)	3.375" (86)	2.625" (67)	3.75" (95)	3.75" (95)
					5" (127)	2.75" (70)	—	2.625" (67)	3.75" (95)	—
					6" (152)	3.25" (83)	4.75" (121)	—	—	—

MIFAB

FOR CATALOGUE USE ONLY



SCALE : 1 : 4

in/[mm]

GENERAL TOLERANCE :
 LINEAR : N/A
 ANGULAR : N/A
 UNLESS OTHERWISE SPECIFIED

P/N :

F1100-C-SD

SHEET : 1 OF 1

A5

REV :

0