


F1100-C

SCALE 1 : 4

STRAINER DIAMETER	STRAINER ADJUSTMENT		ANSI/ASME RATING		PIPE SIZE	NO HUB	BODY HEIGHT PUSH ON (P)	THREADED (T)	INSIDE CAULK (X)	PVC/ABS (-30/-31)
	MIN	MAX	FREE AREA SQ IN	LOAD RATING						
5"(127)	1.56"(40)	2.69"(68)	8 SQ IN	UPTD	2"(51)	2.75"(70)	3.375"(86)	2.25"(57)	3.75"(95)	2.94"(75)
6"(152)	1.69"(43)	2.63"(67)	9 SQ IN	NB(-1) 2,000 LBS	3"(76)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
7"(178)	1.5"(38)	2.63"(67)	12 SQ IN	SS(-3) 5,000 LBS TO DI(-4) 7,499 LBS	4"(102)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
8"(203)	1.88"(48)	2.75"(70)	18 SQ IN		5"(127)	2.75"(70)	—	2.625"(67)	3.75"(95)	—
10"(254)	1.88"(48)	2.75"(70)	26 SQ IN	6"(152)	3.25"(83)	4.75"(121)	—	—	—	

**MIFAB**

FOR CATALOGUE USE ONLY



SCALE : 1 : 4

in/[mm]

GENERAL TOLERANCE :  
 LINEAR : N/A  
 ANGULAR : N/A  
 UNLESS OTHERWISE SPECIFIED

P/N :

F1100-C

SHEET : 1 OF 1

A5

REV :

0