


F1120
SCALE 1 : 4

STRAINER DIAMETER	STRAINER ADJUSTMENT		FREE AREA SQ IN	ANSI/ASME RATING LOAD RATING			BODY HEIGHT		
	MIN	MAX		NB(-1)	SS(-3)	DI(-4)	PIPE SIZE (THREADED NPT)	A	B
5"(127)	0.5"(13)	1.5"(38)	8 SQ IN	UPTD 2,000 LBS	5,000 LBS TO 7,499 LBS	5,000-7,499 LBS	2"(51)	2.25"(57)	5.1875"(132)
6"(152)	0.69"(17)	1.5"(38)	9 SQ IN			---	---	---	---
7"(178)	0.56"(14)	1.56"(40)	12 SQ IN	---	---	---	3"(76)	2.5"(64)	5.1875"(132)
8"(203)	0.69"(17)	2.25"(57)	18 SQ IN	---	---	5,000-7,499 LBS	---	---	---
10"(254)	0.69"(17)	2.25"(57)	26 SQ IN	---	---	---	4"(102)	2.75"(70)	8.375"(213)

MIFAB

FOR CATALOGUE USE ONLY



SCALE : 1 : 4

in/[mm]

GENERAL TOLERANCE :
LINEAR : N/A
ANGULAR : N/A
UNLESS OTHERWISE SPECIFIED

P/N :

F1120

SHEET : 1 OF 1

A5

REV :

0