


C1100-RFC

SCALE 1 : 4

TOP ASSEMBLY DIAMETER	TOP ASSEMBLY ADJUSTMENT		ANSI/ASME RATING LOADRATING SS(-3)	PIPE SIZE	NO HUB	BODY HEIGHT			PVC/ABS (-30/-31)
	MIN	MAX				PUSH ØN(P)	THREADED (T)	INSIDE CAULK (X)	
7"(178)	1.125"(29)	1.88"(88)	5000 TD	2"(51)	2.75"(70)	3.375"(86)	2.25"(57)	3.75"(95)	2.94"(75)
				3"(76)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
				4"(102)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
9"(229)	1.125"(29)	1.88"(88)	7499 LBS	5"(127)	3.25"(83)	—	2.625"(67)	3.75"(95)	—
				6"(152)	3.25"(83)	—	—	—	—

MIFAB

FOR CATALOGUE USE ONLY



SCALE : 1 : 4

in/[mm]

GENERAL TOLERANCE :

LINEAR : N/A

ANGULAR : N/A

UNLESS OTHERWISE SPECIFIED

P/N :

C1100-RFC

REV :

0

SHEET : 1 OF 1

A5