



Tuesday, July 27, 2021 8:50:56 AM

# POWERLIFT STANDARD HEAD DETAIL (DOUBLE TRUSS WOOD BUILDING HEAD MEMBER)



SECTION A-A  
SCALE 1 : 8

**PROPRIETARY AND CONFIDENTIAL**

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF POWERLIFT DOORS. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF POWERLIFT DOORS IS PROHIBITED.



		UNLESS OTHERWISE SPECIFIED:		NAME	DATE
		DIMENSIONS ARE IN INCHES	DRAWN		
		TOLERANCES:	CHECKED		
		FRACTIONAL ±	ENG APPR.		
		ANGULAR: MACH ± BEND ±	MFG APPR.		
		TWO PLACE DECIMAL ±	Q.A.		
		THREE PLACE DECIMAL ±	COMMENTS:		
		INTERPRET GEOMETRIC TOLERANCING PER: ASME Y14. 5-2009			
		MATERIAL			
		FINISH			
NEXT ASSY	USED ON				
APPLICATION		DO NOT SCALE DRAWING			

Part Number	N/A	
TITLE:	Wood Jamb and Double Truss Header	
SIZE	Door Type(s)	REV
<b>A</b>	Standard	A
SCALE: 1:25	WEIGHT:	SHEET 1 OF 3

B

B

A



A

Tuesday, July 27, 2021 8:50:56 AM

# POWERLIFT STANDARD JAMB DETAIL (WOOD BUILDING JAMB MEMBER)

B

B



BUILDING JAMB  
2X10 OR LARGER MEMBERS  
BY OTHERS  
(SIZE AND RELATIVE  
LOCATION MAY VARY)

POWERLIFT OUTSIDE  
FRAME POST MEMBER

POWERLIFT CYLINDER

WOOD LAGS SPACED  
18" MAX ON-CENTER  
TYP 1/2" DIA. WOOD LAG  
(SIZE MAY VARY)

POWERLIFT OUTSIDE  
DOOR LEG MEMBER

POWERLIFT DOOR  
BOTTOM TRUSS MEMBER

SECTION B-B  
SCALE 1 : 10

### PROPRIETARY AND CONFIDENTIAL

THE INFORMATION CONTAINED  
IN THIS DRAWING IS THE SOLE  
PROPERTY OF POWERLIFT  
DOORS. ANY REPRODUCTION  
IN PART OR AS A WHOLE  
WITHOUT THE WRITTEN  
PERMISSION OF POWERLIFT  
DOORS IS PROHIBITED.



		UNLESS OTHERWISE SPECIFIED:		NAME	DATE
		DIMENSIONS ARE IN INCHES	DRAWN		
		TOLERANCES:	CHECKED		
		FRACTIONAL ±	ENG APPR.		
		ANGULAR: MACH ± BEND ±	MFG APPR.		
		TWO PLACE DECIMAL ±	Q.A.		
		THREE PLACE DECIMAL ±	COMMENTS:		
		INTERPRET GEOMETRIC TOLERANCING PER: ASME Y14. 5-2009			
		MATERIAL			
		FINISH			
NEXT ASSY	USED ON				
APPLICATION		DO NOT SCALE DRAWING			

Part Number	N/A	
TITLE:	Wood Jamb and Double Truss Header	
SIZE	Door Type(s)	REV
<b>A</b>	Standard	A
SCALE: 1:25	WEIGHT:	SHEET 2 OF 3



A

A

# POWERLIFT STANDARD SILL DETAIL

B

B



SECTION C-C  
SCALE 1 : 10

A

A

**PROPRIETARY AND CONFIDENTIAL**  
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF POWERLIFT DOORS. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF POWERLIFT DOORS IS PROHIBITED.



		UNLESS OTHERWISE SPECIFIED:		NAME	DATE
		DIMENSIONS ARE IN INCHES	DRAWN		
		TOLERANCES:	CHECKED		
		FRACTIONAL ±	ENG APPR.		
		ANGULAR: MACH ± BEND ±	MFG APPR.		
		TWO PLACE DECIMAL ±	Q.A.		
		THREE PLACE DECIMAL ±	COMMENTS:		
		INTERPRET GEOMETRIC TOLERANCING PER: ASME Y14. 5-2009			
		MATERIAL			
		FINISH			
NEXT ASSY	USED ON				
APPLICATION		DO NOT SCALE DRAWING			

Part Number	N/A	
TITLE:	Wood Jamb and Double Truss Header	
SIZE	Door Type(s)	REV
<b>A</b>	Standard	A
SCALE: 1:25	WEIGHT:	SHEET 3 OF 3