


C1100-T

SCALE 1 : 4

TOP ASSEMBLY DIAMETER	TOP ASSEMBLY ADJUSTMENT MIN MAX		ANSI/ASME LOAD RATING	PIPE SIZE	NO HUB	BODY HEIGHT PUSH ON(P)	THREADED (T)	INSIDE CAULK (X)	PVC/ABS (-30/-31)
5"(125)	0.5"(13)	1.25"(32)	NB(-1) 2000 TO 4999LBS	2"(51)	2.75"(70)	3.375"(86)	2.25"(57)	3.75"(95)	2.94"(75)
				3"(76)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
				4"(102)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
			SS(-3) 5000 TO 7499LBS	5"(127)	3.25"(83)	—	2.625"(67)	3.75"(95)	—
				6"(152)	3.25"(83)	—	—	—	—

MIFAB

FOR CATALOGUE USE ONLY



SCALE : 1 : 4

in/[mm]

SHEET : 1 OF 1

A5

GENERAL TOLERANCE :
LINEAR : N/A
ANGULAR : N/A
UNLESS OTHERWISE SPECIFIED

P/N :

C1100-T

REV :

0