




TYPICAL LAYOUT – BRICKLAYER PATTERN



TYPICAL LAYOUT – HERRINGBONE PATTERN

GEOBLOCK 5150 MATERIAL SPECIFICATION	
MATERIAL	UP TO 100% RECYCLED POLYETHYLENE
COLOR	RANGES DARK SHADES GRAY TO BLACK
CHEMICAL RESISTANCE	SUPERIOR
CARBON BLACK FOR UV STABILIZATION, %	1.5 TO 2.0%
UNIT MIN CRUSH STRENGTH – EMPTY @ 70F (21C)	420 PSI (2,900 KPa)
UNIT MIN CRUSH STRENGTH – SAND FILLED @ 70F (21C)	7,058 PSI (48,734 KPa)
FLEXURAL MODULUS @ 73F (21C)	35,000 PSI (240,000 KPa)
NOMINAL DIMENSIONS – WIDTH X LENGTH	20 X 40 IN (0.5 X 1.0 M)
NOMINAL UNIT DEPTH	2 IN (50 MM)
NOMINAL AREA	5.3 SQFT (0.5 SQMTR)
CELLS PER UNIT	72
CELL SIZE	3.1 X 3.2 IN (79 X 81 MM)
TOP OPEN AREA PER UNIT	87%
BOTTOM OPEN AREA PER UNIT	41%
INTERLOCKING OFFSET SHEAR TRANSFER PINS	12 TABS PER 40 IN (PER 1 M)
NOMINAL WEIGHT PER UNIT	8.7 LBS (4.0 KG)
RUNOFF COEFFICIENT @ 2.5 IN/HR (64 MM) RAIN	0.15
UNITS PER PALLET	50



REYNOLDS PRESTO®  
 PRODUCTS, INC.  
 670 NORTH PERKINS STREET  
 APPLETON, WI 54914  
 920-738-1342  
 WWW.PRESTOGEO.COM

**GEOBLOCK 5150  
 POROUS PAVEMENT SYSTEM**

PRESTO®, GEOSYSTEMS®, AND GEOBLOCK® ARE REGISTERED TRADEMARKS OF REYNOLDS PRESTO PRODUCTS, INC.

DATE:	MARCH 2020	FILE NAME	GB5150A1.dwg
SCALE:	NTS	SHEET	1