


C1100-TS

SCALE 1 : 4

COVER SIZE SQUARE	TOP ASSEMBLY ADJUSTMENT		ANSI/ASME LOAD RATING	PIPE SIZE	NO HUB	BODY HEIGHT		INSIDE CAULK (X)	PVC/ABS (-30/-31)
	MIN	MAX				PUSH IN(P)	THREADED (T)		
5" (127) X 5" (127)	0.5" (13)	1.25" (32)	NB(-1) 2000 TO 4999LBS	2" (51)	2.75" (70)	3.375" (86)	2.25" (57)	3.75" (95)	2.94" (75)
				3" (76)	2.75" (70)	3.375" (86)	2.625" (67)	3.75" (95)	3.75" (95)
			SS(-3) 5000 TO 7499LBS	4" (102)	2.75" (70)	3.375" (86)	2.625" (67)	3.75" (95)	3.75" (95)
				5" (127)	3.25" (83)	—	2.625" (67)	3.75" (95)	—
			6" (152)	3.25" (83)	—	—	—	—	

MIFAB

FOR CATALOGUE USE ONLY



SCALE : 1 : 4

in/[mm]

GENERAL TOLERANCE :
 LINEAR : N/A
 ANGULAR : N/A
 UNLESS OTHERWISE SPECIFIED

P/N :

C1100-TS

SHEET : 1 OF 1

A5

REV :

0