


C1220

SCALE 1 : 4

TOP ASSEMBLY DIAMETER	TOP ASSEMBLY ADJUSTMENT		ANSI/ASME LOAD RATING	PIPE SIZE	NO HUB	BODY HEIGHT	
	MIN	MAX				PUSH DN(P)	PVC/ABS (-30/-31)
5"(127)	0.75"(19)	2.063"(52)	2000 TO 4,999LBS NB(-1)	2"(51)	4"(102)	4.375"(111)	4.375"(111)
			5000 TO 7,499LBS SS(-3)	3"(76)	4"(102)	4.375"(111)	4.375"(111)
			5000 TO 7,499LBS DI(-4)	4"(102)	4"(102)	4.375"(111)	4.375"(111)

MIFAB

FOR CATALOGUE USE ONLY



SCALE : 1 : 4

in/[mm]

GENERAL TOLERANCE :

LINEAR : N/A

ANGULAR : N/A

UNLESS OTHERWISE SPECIFIED

P/N :

C1220

SHEET : 1 OF 1

A5

REV :

0