


Boral Steel® Architectural Details are divided into three (3) categories based on the install method used:

Architectural details provided for Boral Steel® customers only

BATTEN (Panel is exposed fastened & mounted onto a wood 2x2 batten or steel hat channel)

DIRECT (Panel is exposed fastened & mounted Direct-to-the roof-deck)

GRANITE-RIDGE Shingle (Panel is hidden fastened & mounted Direct-to-the roof-deck)



Panels: Cut and bend panel on angle and turn down into valley.

Roofing Underlayment:

1. Install one layer continuous down valley
2. Install field material to prevailing building code
3. Strip in valley with self-adhering underlayment a minimum 3" into valley and minimum 3" onto underlayment

Boral Steel 5 "V" Valley:
Fasten both sides at 24" O.C. minimum. Fastener to penetrate decking a minimum of $\frac{3}{8}$ ".
Extend valley $\frac{1}{2}$ " minimum beyond fascia.

Profiles:

PINE-CREST Shake

BARREL-VAULT Tile

PACIFIC Tile

COTTAGE Shingle

**Direct
Open 5"V" Valley**

Boral Steel Stone Coated Roofing
7575 Irvine Ctr Dr Suite 100, Irvine, CA 92618

**Drawings
are not to
scale**