

Boral Steel® Architectural Details are divided into three (3) categories based on the install method used:

BATTEN (Panel is exposed fastened & mounted onto a wood 2x2 batten or steel hat channel)

DIRECT (Panel is exposed fastened & mounted Direct-to-the roof-deck)

GRANITE-RIDGE Shingle (Panel is hidden fastened & mounted Direct-to-the roof-deck)

Architectural details provided for Boral Steel® customers only

***Panel fastener lengths have been exaggerated to show that they must penetrate the decking and/or structural member.**


Panels: Install bottom panel to extend past fascia $\frac{1}{2}$ ". Seal and chip screws at top surface of panel. Nose and hidden fastener must penetrate the decking a minimum of $\frac{3}{8}$ ". The nose fastener does not require sealant.

Eave Riser: Boral Steel Eave Riser Metal. Fasten 12" O.C. with 16d corrosion resistant nails or screws with enough length to penetrate decking a minimum of $\frac{3}{4}$ ".

Roofing Underlayment: Install new underlayment over existing shingle roofing. Wrap minimum 1" over finish edges.

Existing Shingle: Cut back edges to be flush with eave. Removal of existing drip edge may be necessary.

Boral Steel Drip-edge Metal: Install tight to structure.



Profiles:

PINE-CREST Shake

BARREL-VAULT Tile

PACIFIC Tile

COTTAGE Shingle

**Direct
Eave over Existing Roofing**

Boral Steel Stone Coated Roofing
7575 Irvine Ctr Dr Suite 100, Irvine, CA 92618

Drawings
are not to
scale