



**EconoDrain® Series #8**  
STANDARD EPS FORMS




**EconoDrain® Series #8**  
GRATE SELECTION



**EconoDrain® Series #8**  
FINISHED PLAN VIEW











EPS FORM	MIN DEPTH	MAX	FLOW GPM
06	6"	6 1/2"	281
07	6 1/2"	7"	325
08	7"	7 1/2"	370
09	7 1/2"	8"	415
10	8"	8 1/2"	461
11	8 1/2"	9"	507
12	9"	9 1/2"	554
13	9 1/2"	10"	601
14	10"	10 1/2"	648
15	10 1/2"	11"	695
16	11"	11 1/2"	742
17	11 1/2"	12"	790
18	12"	12 1/2"	838
19	12 1/2"	13"	886
20	13"	13 1/2"	934
21	13 1/2"	14"	982
22	14"	14 1/2"	1030
23	14 1/2"	15"	1078
24	15"	15 1/2"	1126
25	15 1/2"	16"	1175
26	16"	16 1/2"	1223
27	16 1/2"	17"	1272
28	17"	17 1/2"	1320
29	17 1/2"	18"	1369
30	18"	18 1/2"	1418
31	18 1/2"	19"	1466
32	19"	19 1/2"	1515
33	19 1/2"	20"	1564
34	20"	20 1/2"	1613
35	20 1/2"	21"	1662
36	21"	21 1/2"	1710
37	21 1/2"	22"	1759
38	22"	22 1/2"	1808
39	22 1/2"	23"	1857
40	23"	23 1/2"	1906
41	23 1/2"	24"	1955
42	24"	24 1/2"	2004
43	24 1/2"	25"	2053
44	25"	25 1/2"	2102
45	25 1/2"	26"	2151

EPS FORM CHART



NOTES TO THE SPECIFIER:  
1. ADD REBAR AS REQUIRED.  
2. SPECIFY MINIMUM CONCRETE ENCASEMENT.  
3. 4" MINIMUM CONCRETE COVERAGE OF OUTLET PIPE IS RECOMMENDED (LABELED WITH "I").  
4. FINAL CONCRETE THICKNESS PER LOCAL ENGINEERING REGULATIONS AND GUIDELINES.

CONSTRUCTION NOTES:  
1. INSTALLATION TO BE COMPLETED IN ACCORDANCE WITH MANUFACTURERS SPECIFICATIONS.  
2. SECURE OUTLET PIPE PRIOR TO CONCRETING OPERATIONS.  
3. FOR ILLUSTRATION ONLY - DO NOT SCALE



GENERAL NOTES:  
1. ALL DIMENSIONS SHOWN ARE NOMINAL.  
2. THIS SYSTEM AVAILABLE WITH PRE-WELDED GRATE FRAMES (STANDARD) OR RAILS WITH OPTIONAL BOLT-IN PLACE SPACER BARS.

**EconoDrain® Series #8**  
ENGINEERING / CONSTRUCTION DETAIL TEMPLATE  
© 2014 MultiDrain Systems, Inc.