


1. ALL DIMENSIONS ARE IN INCHES, UNLESS SPECIFIED OTHERWISE.
2. DIMENSIONS IN PARATHENSIS REPRESENT REFERENCE DIMENSIONS
3. MATERIAL SUBSTITUTIONS ALLOWED WITH WRITTEN APPROVAL ONLY.
4. BREAK ALL SHARP CORNERS AND REMOVE ANY BURRS.
5. PART TO BE FREE OF ANY VISIBLE STRESS CRACKS.
6. CRC DRAWN TO .0566" MIN. MATERIAL THICKNESS.
7. CRC IS SYMMETRICAL ABOUT CENTER LINE.
8. * REPRESENTS VIRTUAL SHARP.

SECTION B-B
SCALE 1:8128



THE DRAWING AND ALL OTHER INFORMATION CONTAINED HEREIN ARE THE CONFIDENTIAL PROPRIETARY PROPERTY OF TELLING INDUSTRIES. THIS DRAWING INFORMATION, IN WHOLE OR IN PART, MAY NOT BE COPIED IN ANY MANNER OR DISCLOSED TO ANYONE WITHOUT PRIOR WRITTEN CONSENT OF TELLING INDUSTRIES. DISCLOSURE OF ANY DRAWING OR INFORMATION IS INTENDED NOT TO AND SHALL NOT OPERATE AS A LICENSE OR AUTHORIZATION TO USE IT FOR ANY PURPOSE WITHOUT SPECIFIC WRITTEN CONSENT OF TELLING INDUSTRIES.

 TELLING 	TOLERANCE: X = ±.060 .XX = ±.015 .XXX = ±.005 ANGLES = ±1°	PROJECT <div>0007</div>			
	TITLE <div>COLD ROLLED CHANNEL (CRC) FOR 16" & 24" STUD SPACING</div>				
	MATERIAL: .0566" MIN. SS GRADE 33 FINISH: G60, PER ASTM A653				
	FLAT FOR TOOL MAKER REFERENCE ONLY				
APPROVED C.HABA	11/8/19	SIZE	CODE	DWG NO	REV
CHECKED C.HABA	11/8/19	C		CRC_B_0008	A
DRAWN S.LEECH	11/8/19	SCALE 1:4	WEIGHT	SHEET 2/2	