




iMotion® TN 110 IN-FLOOR SWING DOOR DRIVE FOR SLENDER PROFILE RAILS: SURFACE MOUNT - STAINLESS STEEL COVER


PAIR DOOR CENTER PIVOT APPLICATION







SURFACE FLOOR BOX w/ STAINLESS STEEL COVER








- Concrete or Finished Floor
- (1) Possible Electrical Feed





REFER TO APPENDIX DWGS FOR BOTTOM DOOR CLEARANCES, RAIL PROFILES & PIVOTS

NOTES:

- 1. DETAILS NOT TO SCALE.
- ELECTRICAL REQUIREMENTS:
 120VAC, 15AMP MIN. TO EACH CONTROLLER LOCATED REMOTE FROM OPERATOR. LOW
 VOLTAGE CONDUIT RUN FROM EACH CONTROLLER TO OPERATOR BY ELECTRICAL CONTRACTOR.
- 3. DOORS, FRAMES AND HARDWARE BY OTHERS. BOTTOM DOOR PIVOT BY TORMAX.
- 4. 32" CLEAR DOOR OPENING REQUIRED TO MEET A.D.A. REQUIREMENTS.
- 5. DOORS MUST BE NON-LATCHED FOR PROPER OPERATION.
- 6. OPERATOR CAN BE CONFIGURED TO MEET ANSI STANDARDS A156.10 & ANSI A156.19