## Executive Design Specifications-System With Recessed Side Track




## CROSS SECTIONAL VIEW OF THE FULLY ASSEMBLED RECESSED SIDE TRACK (V3)

(Scale: 1:1)

-1-3/8"-

1/4" - 3-1/8" - 5-1/2"

ROLLER MOUNTING ANGLE FOR 4" and 5" ROLLERS (Not Drawn To Scale)




(Based On Compression)

CROSS SECTIONAL VIEW OF THE SLIDE BAR AND 4" BOTTOM SEAL

Scale: 1:1

All components are color matched except Mesh, Rivets, and Bottom Seal.



G(R)

- $\textbf{A} \quad \text{Roller Assembly (4" or 5") c/w Inserts (L \& R)}$
- **B** PVC Coated Fiberglass Mesh or other see Mesh Specifications
- C Recessed Side Track Assembly (1-3/8"W x 2-7/64"D)
- D #8 or #10 Corrosion Resistant Fastener
  Type and length of screws may
  vary depending on type of mounting surface
  (Minimum of 3 per Side Track and Roller Mounting Angle)
- E Slide Bar c/w Probe Assembly
- F Bottom Seal 4" Shown (Other options available)
- **G** Roller Mounting Bracket (2" x 5-1/2" x 1/4" x 3-1/8" W)

2	Modify the position of the U-Channel in relation to the Mounting Bracket			N.D.R.	01/27/16
1	Change Slide Bar and Probe to Universal Version			N.D.R.	
Rev#	v # Description of Revision			Approved by Rev Date	
Creator:		Date:	Approved		
NDR		06/17/2013			
Drawing Title:					
PSEXECPRODDESIGNSPEC07(A)					
				Scale	:
© 2013 Phantom Mfg. Intl Ltd.				As	Shown