



- STRUCTURAL SUPPORT (BY OTHERS)
- POLYURATHANE SEALANT (BY OTHERS)
- STAINLESS STEEL DRAWBAND
- 1/4" [6mm] MIN. CLEARANCE TO RAIN COLLAR
- SHEET METAL RAIN HOOD OVERLAPPING FLASHING COLLAR BY 4"
- SHEET METAL FLASHING COVER MINIMUM OF 8" [ABOVE ROOFING MEMBRANE]
- 1/4" MINIMUM CLEARANCE BETWEEN FLASHING COLLAR AND SUPPORT
- APPROVED SEALANT AT PENETRATION/MEMBRANE TRANSITION
- INTERPLY MEMBRANE STRIP-IN
- CAP SHEET MEMBRANE
- 6" [152mm] MINIMUM FLANGE SET IN APPROVED SEALANT; PRIME FLANGE BEFORE STRIPPING
- BASE & INTERPLY MEMBRANES
- INSULATION/COVERBOARD AS APPLICABLE
- RIGID INSULATION OR APPROVED SUBSTRATE
- STRUCTURAL DECK

- NOTES:
1. ATTACH WOOD NAILER TO WALL/DECK IN ACCORDANCE WITH FMRC GUIDELINES, AS PER SECTION 1-28, REGARDING WINDLOADS TO ROOF SYSTEMS AND DECK SECUREMENT.
 2. WOOD BLOCKING MAY BE SLOTTED FOR VENTING OF WET-FILL DECKS OR OTHER APPLICABLE CONSTRUCTIONS.
 3. POLYGLASS RECOMMENDS ALL ROOF EDGE TERMINATIONS BE DESIGNED AND INSTALLED IN ACCORDANCE WITH ANSI/SPRI ES-1.

TYPICAL RAIN COLLAR/PENTRATION DETAIL

NUMBER:
PG-PEN-005

DATE:
July 2011



Polyglass USA, Inc.
1111 W. Newport Center Dr.
Deerfield Beach, FL 33442
www.polyglass.com