| **** | | | | |
|------|---|-----|---|----------------|
| TO | R | M | A | N _© |
| | | JMA | | |

IMOTION 1301 SWING DOOR OPERATOR

SINGLE DOOR, VISIBLE R.H. INSWING CENTER PIVOT NON-PANIC APPLICATION DATE: JOB NAME: _ DOOR NO: _____SHEET DOOR LOCATION:___ DF_ ELECTRICAL --CONTROLS---ELECTRICAL -CONTROLS CU SERIES 200 SIDE LOAD (1)**HEADER** ACCESS COVER--5<u>9</u> [142]iMotion ® 1301 SWING -1¹/₄ [32] 4⁹/₁₆ [116] **DOOR OPERATOR** ┌1<u>1</u> [28] **(2)** -3 € [90]- 18 [48]-**SWING ELEVATION** REVEAL - DISTANCE FROM THE FACE OF THE DOOR TO THE -**EXTERIOR** REAR OF OPERATOR 0"-6" (0-152) VERTICAL SECTION -4 1/2"(114) ⊊ PIVOT 3 3/4"(95) 9 7/16" (240) € OF PIVOT TO Q OP SHAFT INTERIOR **PLAN** DOOR OPENING MIN. - 31" (787) - MAX 49" (1244) **—31 1/2"(800)**— VISIBLE HEADER -2 HORIZONTAL SECTION CASE ABOVE NOTES: 1. DETAILS NOT TO SCALE.
2. ELECTRICAL REQUIREMENTS:
120VAC, 5AMPS MIN. TO OPERATOR BY ELECTICAL CONTRACTOR.
3. DOORS, FRAMES AND HARDWARE BY OTHERS. 4. 32" CLEAR DOOR OPENING REQUIRED TO MEET A.D.A. REQUIREMENTS. 5. DOORS MUST BE NON-LATCHED FOR PROPER OPERATION.

- 6. OPERATOR HEADER IS AVAILABLE FOR FULL WIDTH DOOR APPLICATIONS.
 7. OPERATOR CAN BE CONFIGURED TO MEET ANSI STANDARDS A156.10 & ANSI A156.19
 8. DOOR CLOSED STOP REQUIRED BY OTHERS FOR INSWING DOOR.